


To adequate DC Power Supply (use either Barrel Plug for 5A or + and - screw terminals for 8A capability.

LocoNet Network to other LocoNet devices. Devices can be connected to A,B, or C



- Notes:
1. Any DT4xx throttle can be used to access all features of the DCS240. Any throttle can be used to run trains. The DT402 is shown here.
 2. Throttles can be plugged into any LocoNet jack on the system including attached Universal Panels.
 3. Throttles can also be operated as IR tetherless or Radio.

DCS240 Quick Start Hook Up